



**Undertone®**

31-1/2" undermount double-bowl kitchen sink  
**K-3351**

### Features

- 36" minimum base cabinet width
- Double-equal bowls
- 9-1/2" depth left bowl and 7-1/2" depth right bowl
- Rear drain placement increases cabinet storage space underneath sink
- Includes installation hardware

### Material

- Premium 18-gauge stainless steel

### Installation

- Undermount

### Recommended Products/Accessories

- K-6388 Sink Rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

### Optional Products/Accessories

- K-11352 Disposal Flange with Stopper



### Codes/Standards

ASME A112.19.3/CSA B45.4  
IAPMO Certification

### **KOHLER® Stainless Steel Sinks Lifetime Limited Warranty**

See website for detailed warranty information.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

10-14-2024 21:40 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



## Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 14" (356 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 9-1/2" (241 mm)  
Water depth: 9-1/2" (241 mm)

Bowl area (Right): Length: 14" (356 mm)  
Width: 15-3/4" (400 mm)  
Bowl depth: 7-1/2" (191 mm)  
Water depth: 7-1/2" (191 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1221369-7, required, included

## Notes

Install this product according to the installation instructions.