



Undertone®
30-3/4" undermount double-bowl kitchen sink
K-3355

Features

- 33" (838 mm) minimum base cabinet width
- Large/small bowls with high/low design
- 9-1/2" depth left bowl and 5-1/2" depth right bowl
- Includes installation hardware

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-6389 Sink rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

Included Components

- 91915 Hardware Kit




Codes/Standards

ASME A112.19.3/CSA B45.4

**KOHLER® Stainless Steel Sinks
Lifetime Limited Warranty**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 33" (838 mm)

Bowl area (Right): Length: 9" (229 mm)
 Width: 15" (381 mm)
 Bowl depth: 5-1/2" (140 mm)

Bowl area (Left): Length: 18" (457 mm)
 Width: 18" (457 mm)
 Bowl depth: 9-1/2" (241 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1040559-7, required, included

Notes

Install this product according to the installation instructions.