



Undertone® Preserve®

35-1/4" undermount double-bowl kitchen sink
K-3356-HCF

Features

- 36" minimum base cabinet width
- Extra-large/medium bowls
- 9-1/2" depth left bowl and 7-1/2" depth right bowl
- Innovative Preserve™ sink resists scratching and withstands everyday wear and tear
- Includes installation hardware
- Minimum base cabinet width: 36"–39" (36" may require cabinet modifications)
- Sink drain with strainer sold separately

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-6390 Sink rack for Undertone® Preserve™ sinks
- K-8801 Sink drain and strainer with tailpiece (Qty 2)
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper




Codes/Standards

ASME A112.19.3/CSA B45.4
IAPMO Certification

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 39" (991 mm)

Bowl area (Left): Length: 17-7/8" (454 mm)
Width: 17-7/8" (454 mm)
Bowl depth: 9-1/2" (241 mm)
Water depth: 9-1/2" (241 mm)

Bowl area (Right): Length: 13-3/4" (349 mm)
Width: 15-3/8" (391 mm)
Bowl depth: 7-1/2" (191 mm)
Water depth: 7-1/2" (191 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1217909-7, required, included

Notes

Install this product according to the installation instructions.

Minimum base cabinet width 36" - 39" (36" may require cabinet modifications). Consult an installer for confirmation.