



Undertone®
Under-Mount Kitchen Sink
K-3356-L

Features

- 39" (990 mm) minimum base cabinet width
- Extra-large/medium bowls
- Includes installation hardware

Material

- Premium 18-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- K-6389 Sink rack for Undertone® sinks
- K-6390 Sink rack for Undertone® Preserve™ sinks
- K-8801 Sink drain and strainer with tailpiece (Qty 2)
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper



Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

**KOHLER® Stainless Steel Sinks
Lifetime Limited Warranty**

See website for detailed warranty information.

DISCONTINUED This product has been discontinued.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

10-17-2024 23:52 - US/CA

THE BOLD LOOK
OF **KOHLER®**



Technical Information

All product dimensions are nominal.

Basin configuration: Off-set X-large/small

Min. base cabinet width: 39" (991 mm)

Bowl area (Left): Length: 13-3/4" (349 mm)
Width: 15-3/8" (391 mm)
Bowl depth: 7-1/2" (191 mm)
Water depth: 7-1/2" (191 mm)

Bowl area (Right): Length: 17-7/8" (454 mm)
Width: 17-7/8" (454 mm)
Bowl depth: 9-1/2" (241 mm)
Water depth: 9-1/2" (241 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1221368-7, required, included

Notes

Install this product according to the installation instructions.

Minimum base cabinet width 36" - 39" (36" may require cabinet modifications). Consult an installer for confirmation.