



Staccato™

25" top-mount single-bowl kitchen sink
K-3362-1

Features

- 27" (686 mm) minimum base cabinet width
- Single bowl
- 8" (203 mm) depth
- Single faucet hole
- Includes installation hardware

Material

- Premium 18-gauge stainless steel

Installation

- Top-mount

Recommended Products/Accessories

- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-8803 Manual Sink Basket Strainer
- K-8804 Sink drain body with tailpiece
- K-8813 Stainless steel sink drain and strainer with tailpiece
- K-8814 Stainless steel sink drain and strainer
- K-11352 Disposal Flange with Stopper



Codes/Standards

ASME A112.19.3/CSA B45.4

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

11-3-2024 22:47 - US/CA

THE BOLD LOOK
OF **KOHLER**®



Staccato™
25" top-mount single-bowl kitchen sink
K-3362-1



Technical Information

All product dimensions are nominal.

- Basin configuration: Single Bowl
- Cutout: Top-mount, 24-1/2" x 21-1/2" (622 mm x 546 mm) with 1" (25 mm) radius corners
- Center(s): 8" (203 mm)
- Min. base cabinet width: 27" (686 mm)
- Bowl area: Length: 21-1/8" (537 mm)
Width: 15-11/16" (398 mm)
Bowl depth: 8-5/16" (211 mm)
Water depth: 8" (203 mm)
- Number of deck holes: 1
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 3-5/8" (92 mm)

Notes

Install this product according to the installation instructions.