




Strive®
Smart Divide® 32" undermount double-bowl
workstation kitchen sink
K-33664-PC

Features

- 33" (838 mm) minimum base cabinet width
- Offset, double-bowl sink
- 9" (229 mm) depth provides generous workspace
- Smart Divide® feature offers a lower bowl divider that increases workspace versatility
- Rear drains increase workspace in the sink and storage space underneath
- Rounded 3/8" (10 mm) corners are easy to clean
- SilentShield® sound-absorption technology offers quieter performance
- All included accessories nest neatly together for easy storage when not in use
- Included accessories: cutting board, drain board, colander / drying rack, soaking bin with drain, stainless steel bottom sink rack, drain cover
- Sink drain and strainer sold separately



Codes/Standards

ASME A112.19.3/CSA B45.4

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.

Material

- Premium 16-gauge stainless steel

Installation

- Undermount
- Installation hardware and templates included

Recommended Products/Accessories

K-35484 Three-piece workstation sink prep bowl set
K-35487 Three-piece ice bucket set
K-35488 Ice bucket holder
K-35489 Professional-style cutting board
K-35491 Marble serving tray
K-35485 Workstation sink cover

Optional Products/Accessories


K-8801 Sink drain and strainer with tailpiece
K-11352 Disposal Flange with Stopper
K-23729 Stainless steel cleaner
K-35492 Bar sink cover

Included Components

K-33675 Left-side sink rack for K-33664-PC Strive kitchen sink
K-35478 Three-piece workstation sink accessory set
K-35480 Hardwood cutting board
K-35482 Drain cover



Strive®
Smart Divide® 32" undermount double-bowl
workstation kitchen sink
K-33664-PC



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 33" (838 mm)

Bowl area (Left): Length: 17-1/8" (435 mm)
Width: 15-9/16" (395 mm)
Bowl depth: 9" (229 mm)
Water depth: 9" (229 mm)

Bowl area (Right): Length: 12" (305 mm)
Width: 15-9/16" (395 mm)
Bowl depth: 9" (229 mm)
Water depth: 9" (229 mm)

Drain hole: 3-3/4" (94 mm)

Template: Undermount, 1564888-7, required, included

Notes

Install this product according to the installation instructions.

"NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1- 800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used."