




Collage®
600 mm x 800 mm lighted framed mirrored cabinet
K-33690K-R

Features

- Mirror with embedded LED lighting elevates your bathroom experience
- Approx. 3000 – 6500 Kelvin (exterior frame) and 4000 Kelvin (inside door) light appearances deliver a neutral light ideal for overall bathroom aesthetics as well as tasks
- Minimum 90 CRI (color rendering index) lets you see yourself in the truest light for makeup application, grooming, and skin care
- Integrated LED bulbs have an estimated life expectancy of 30,000 hours
- Touch-control bar integrated within frame design
- Clever: Touchless sensor-activated lighting
- Built-in dimmer
- Front mirror and inside door mirror provide superior visibility
- Defogging feature ensures reflection visibility — even in high humidity
- Custom compartments for holding makeup brushes and other makeup items
- Hair dryer holder to keep grooming tools organized
- Electrical outlet allows users to plug in hair stylers and other grooming tools
- Cord organizer prevents grooming tools from becoming tangled
- One adjustable tempered-glass shelf
- Two partial sliding utility bar shelves
- 125° door swing with soft-close hinges



Codes/Standards

None Applicable

See website for detailed warranty information.

Material

- Black anodized aluminum frame


Installation

- Reversible: install as left- or right-hinge swing
- Includes mounting hardware for surface installation
- Easy surface-mount installation—no wall cutting
- Recommend professional electrician installation



Collage®

600 mm x 800 mm lighted framed mirrored cabinet
K-33690K-R



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights, Defogger: 220 V, 0.28 A, 50 Hz

Technical Information

All product dimensions are nominal.

Lighting included: Yes

Electrical component rating: LED: 1.5 A, 36 W
Defogger: 0.625 A, 15 W

Notes

Install this product according to the installation instructions.

CAUTION: Risk of property damage. For surface mounting, use anchors (not provided) rated for the loaded weight of this product. Refer to the anchor manufacturer's instructions..

When determining the height of the medicine cabinet, ensure the mirrored door will clear all obstacles (such as a faucet). A minimum distance of 3" (76 mm) is required.