


Features

- Main Cabinet: Mirrored door with reversible hinge and 125° swing, inside door mirror, integrated touch-control frame, built-in LED dimmer, adjustable tempered-glass shelf, two partial sliding utility bar shelves, makeup storage, hair dryer holder, electrical outlet, and cord organizer
- Showcase Cabinet: Framed smoky transparent grey glass door with reversible hinge and 103° swing, interior lighting, two adjustable glass shelves, lower tip-out bottom drawer
- Approx. 3000 – 6500 Kelvin (exterior frame) and 4000 Kelvin (inside door) light appearances deliver a neutral light ideal for overall bathroom aesthetics as well as tasks
- Minimum 90 CRI (color rendering index) lets you see yourself in the truest light for makeup application, grooming, and skin care
- Integrated LED bulbs have an estimated life expectancy of 30,000 hours
- Clever: Touchless sensor-activated lighting
- Defogging feature ensures reflection visibility — even in high humidity
- Soft-close doors prevent slamming

**Codes/Standards**

None Applicable


See website for detailed warranty information.

Material

- Black anodized aluminum frame

Installation

- Reversible: install as left- or right-hinge swing
- Includes mounting hardware for surface installation
- Easy surface-mount installation—no wall cutting
- Recommend professional electrician installation



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights, Lights, 220 V, 0.36 A, 50 Hz
Defogger:

Technical Information

All product dimensions are nominal.

Lighting included: Yes

Electrical component LED: 1.5 A, 36 W
rating: LED: 0.75 A, 18 W
Defogger: 0.625 A, 15 W

Notes

Install this product according to the installation instructions.

This cabinet is designed for either right or left door swing. Check for obstructions.

CAUTION: Risk of property damage.

For surface mounting, use anchors (not provided) rated for the loaded weight of this product. Refer to the anchor manufacturer's instructions.

When determining the height of the medicine cabinet, ensure the mirrored door will clear all obstacles (such as a faucet). A minimum distance of 3" (76 mm) is required.