

Features

- Showcase Cabinet: Framed smoky transparent grey glass door with reversible hinge and 103° swing, interior lighting, two adjustable glass shelves, lower tip-out bottom drawer
- 4000 Kelvin inside door light to display skincare and perfume bottles
- Integrated LED bulbs have an estimated life expectancy of 30,000 hours
- Soft-close door prevents slamming

Material

- Premium metal and glass construction
- Black anodized aluminum frame

Installation


- Reversible: install as left- or right-hinge swing
- Includes mounting hardware for surface installation
- Easy surface-mount installation—no wall cutting
- Recommend professional electrician installation



Codes/Standards

None Applicable

See website for detailed warranty information.



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights: 220 V, 0.11 A, 50 Hz

Technical Information

All product dimensions are nominal.

Lighting included: Yes

Electrical component LED: 0.75 A, 18 W
rating:

Notes

Install this product according to the installation instructions.

CAUTION: Risk of property damage.

For surface mounting, use anchors (not provided) rated for the loaded weight of this product. Refer to the anchor manufacturer's instructions.

When determining the height of the medicine cabinet, ensure the mirrored door will clear all obstacles (such as a faucet). A minimum distance of 3" (76 mm) is required.