

## Features

- 33" (838 mm) minimum base cabinet width
- Single large bowl
- 9" (229 mm) depth provides generous workspace
- Right rear drain placement increases workspace in the sink and storage space underneath
- Rounded 3/8" (10 mm) corners are easy to clean
- Matte finish offers rich, dimensional color
- All included accessories nest neatly together for easy storage when not in use
- Included accessories: cutting board, drain board, colander / drying rack, soaking bin with drain, stainless steel bottom sink rack
- Drain board, colander / drying rack, soaking bin with drain, and bottom sink rack are dishwasher-safe



## Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

## Installation

- Undermount
- Installation hardware and templates included

## Recommended Products/Accessories

- K-35489 HDPE cutting board
- K-35484 Three-piece workstation sink prep bowl set
- K-35491 Marble serving tray
- K-35487 Three-piece ice bucket set
- K-35488 Ice bucket holder
- K-35485 Workstation sink cover

## Optional Products/Accessories

- K-35482 Drain cover
- K-11352 Disposal Flange with Stopper
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23730 Neoroc® cleaner

## Included Components

- K-33715 Sink rack
- K-35478 Three-piece workstation sink accessory set
- K-35480 Hardwood cutting board

## Codes/Standards







CSA B45.5/IAPMO Z124  
IAPMO Certification


## KOHLER® Neoroc® Sinks Lifetime Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CM7	Matte Graphite
	CM6	Matte White
	CM1	Matte Black
	CM4	Matte Grey
	CM3	Matte Taupe
	CM2	Matte Brown



## Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl  
 Min. base cabinet width: 33" (838 mm)

Bowl area (Basin #1):  
 Length: 27-1/4" (692 mm)  
 Width: 15-9/16" (395 mm)  
 Bowl depth: 9" (229 mm)  
 Water depth: 9" (229 mm)

With overflow: No

Drain hole: 3-7/8" (98 mm)

Template: Undermount, 1552903-7, required, included

## Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.