

Features


- Versatile, contemporary design
- Tall height is ideal for vessel-style sinks
- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 5-3/8" (136 mm) spout reach
- 7-7/8" (200 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Aerated flow
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece

Material

- Premium material construction for durability and reliability
- KOHLER[®] finishes resist corrosion and tarnishing

Installation


- Deck-mount
- For single-hole installation
- Preattached flexible supply lines simplify installation



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: Yes

Drain with overflow: Yes

Notes

Install this product according to the installation guide.