

## Poise® | K-3387

33" undermount single-bowl kitchen sink

### Features

- Part of K-3158-NA
- 33" (838 mm) x 18" (457 mm)
- 9" (229 mm) depth provides generous workspace
- Single-basin design
- Undercounter installation
- Please order the K-3158-NA sink which includes the following:  
sink and sink rack



### Sustainability



---

## Codes/Standards

ASME A112.19.3/CSA B45.4

---

## Technical Information

*All product dimensions are nominal.*

Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Single Bowl
Basin Length:	29" (737 mm)
Basin Width:	14" (356 mm)
Basin Depth:	9-1/2" (241 mm)

---

## Material

- Premium 16-gauge stainless steel
- 

## Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

K-8801 Sink drain and strainer with tailpiece

K-8799 Sink drain and strainer basket, less tailpiece


---

## Warranty

*See website for detailed warranty information.*

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





### Installation Notes

Install this product according to the installation instructions.

