

Features

- Part of K-3160-NA
- 33" (838 mm) x 18" (457 mm)
- 9-1/8" depth
- Large/medium bowls
- Undercounter installation
- Please order the K-3160-NA sink which includes the following: sink and sink rack

Material

- Premium 16-gauge stainless steel

Recommended Products/Accessories

- K-3143 Sink Rack
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-3140 Cutting Board
- K-11352 Disposal Flange with Stopper

Included Components

- 91915 Hardware Kit




Codes/Standards

ASME A112.19.3/CSA B45.4
IAPMO Certification

KOHLER® Stainless Steel Sinks

Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Left): Length: 10-11/16" (271 mm)
 Width: 14" (356 mm)
 Bowl depth: 9-1/8" (232 mm)

Bowl area (Right): Length: 18-3/16" (462 mm)
 Width: 14" (356 mm)
 Bowl depth: 9-1/8" (232 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1021992-7, required, included

Notes

Install this product according to the installation instructions.