

KOHLER® Faucets

Radiance™

Shoulder-height two-function showerhead, 12.5 lpm

K-34099IN

Features

- Contemporary design
- Multifunction showerhead with advanced spray engine provides two alternate spray experiences: rain and cascade
- Rain delivers a drenching spray experience, ideal for rinsing soap from body
- Cascade spray delivers a luxurious waterfall-like angled stream for complete rinsing
- Sprayface button switches between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 3.3 gpm (12.5 lpm) maximum flow rate at 43.5 psi (3.0 bar)

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount



Codes/Standards

None Applicable

KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	BRD	Vibrant Brushed Rose Gold
	RGD	Vibrant Rose Gold


Customer Care: 1800 103 2244 (Toll Free)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to <http://www.kohler.co.in>.

10-12-2025 19:40 - IN

THE BOLD LOOK
OF **KOHLER®**



Technical Information

All product dimensions are nominal.

Shower/Rainhead rated max flow: 4 gal/min (15.1 l/min)

Pressure/fixture Supply Requirements

Fixture pressure 80 psi (551.6 kPa)
max (static):

Fixture pressure min 29 psi (199.9 kPa)
(static):

Min flowing 29 psi (199.9 kPa)
pressure:

Min flow rate: 80 gpm (302.8 lpm)

Notes

Install this product according to the installation instructions.