



Leap™
One-piece elongated smart toilet with front bidet wand
technology, dual-flush
K-34281

Features

- Integrated dual-wand bidet toilet seat, with rear and innovative front wand technology
- Stainless steel wands offers adjustable spray shape, position, water pressure, temperature, pulsate, and oscillate functions
- Self-cleaning function uses UV light to automatically clean rear wand surface
- Heated seat with adjustable temperature settings
- Warm-air drying system with adjustable temperature settings
- Automatic deodorization system for odor control
- Sleek, handheld remote control with four programmable user presets
- Emergency flush supports up to 100 flushes during power outage with simple touch-button activation
- Dual-flush offers a choice of 1.0 or 1.28 gpf (3.4 or 4.8 lpf)
- Energy Save feature monitors usage and adjusts heated seat settings to save energy
- Slim, contemporary one-piece smart toilet with integrated personal cleansing
- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Designed to support easier transfers from wheelchair
- Easy installation system provides a simple solution for skirted toilets
- Includes complete toilet and seat, supply stop valve, braided inlet supply hose, power cord, and remote control
- Quiet-Close™ elongated lid and seat prevents slamming
- Front and rear wash modes provide warm water for cleansing
- Motion-activated, hands-free opening/closing of cover
- Automatic flushing after every use; flush can also be controlled by the remote control or backup button

Installation

- Standard 12" (305 mm) rough-in
- Requires dedicated electrical GFCI circuit (120 V, 15 A, 60 Hz)
- Requires connection to toilet water supply line



ADA	CSA B651	OBC
------------	-----------------	------------

Codes/Standards

ASME A112.19.2/CSA B45.1
 ASME A112.4.2/CSA B45.16
 DOE - Energy Policy Act 1992
 EPA WaterSense®
 California Energy Commission (CEC)
 UL 1951
 CSA C22.2 No. 14
 CSA C22.2 No. 68
 ADA
 ICC/ANSI A117.1
 CSA B651
 OBC


**KOHLER® Intelligent Toilet and C3®
 Cleansing Seat Three-Year Limited
 Warranty**

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Power
Seat hinge type:	Self-raising
Trap passageway:	2" (51 mm)
Rim to water surface:	5-3/4" (146 mm)
Rough-in:	12" (305 mm)
Template:	Footprint, 1601231, required, included

Fixture Supply Requirements

Min static pressure: 30 psi (206.8 kPa)

Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation instructions.

IMPORTANT! Use the supply hoses provided with the fixture. Do not reuse the previously installed hoses.

Maximum inlet water temperature shall not exceed 80°F (26.7°C).

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.