

### Features

- Three fan control speed settings (100, 130, 150 CFM) with standard 6" (152 mm) air duct. CFM will vary with 4" (102 mm) air duct
- Lowest speed operates at a whisper-quiet 0.4 sones with standard 6" (152 mm) air duct and at 0.6 sones with 4" (102 mm) air duct
- Remote control controls on/off and fan speed
- Download the KOHLER Konnect® app for additional functionality, such as creating an automatic on/off run schedule, or controlling fan speed and humidity sensor setting
- Remote control mounts anywhere in bathroom, even over existing fan switch
- Fits standard bathroom exhaust fan cutouts to make upgrading easy
- 6" to 4" duct reducer ensures airflow efficiency by creating connection between air duct openings of two different sizes
- Box contains fan, remote control, 6" to 4" air duct reducer, two CR2032 3V lithium coin cell batteries, mounting hardware

### Installation

- Ceiling-mount






### Codes/Standards

UL 507  
CSA C22.2 No. 113  
ENERGY STAR®  
cUL Listed

### KOHLER® Bath Fan Three-Year Limited Warranty

See website for detailed warranty information.



### Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Blower: 120 V, 15 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Material: Steel, Plastic

Height: 3-1/8" (79 mm) - 3-1/8" (79 mm)

Electrical component rating: Blower: 60 Hz

### Notes

Install this product according to the installation instructions.