

Features

- Single-function rainhead
- Ultra-slim design
- Optimized sprayface for maximum performance
- Angled nozzles provide a full-coverage spray
- Adjustable swivel ball joint allows for precise spray adjustment
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Flexible, silicone nozzles assure long life and easy clean
- 2.5 gpm (9.5 lpm) maximum flow rate at 80 psi (5.5 bar)
- G 1/2 connection

Material


- Stainless steel construction
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray



Installation

- Installs as a ceiling or wall mount application
- Requires single-function rainhead shower arm and flange (sold separately)

**Codes/Standards**

Plumbing Standards
GB/T 23447

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 2.8 gal/min (10.6 l/min)

Notes

Install this product according to the installation guide.