



Parallel™ | K-35113-SC01

One-light sconce

Features

- Etched opal glass gently diffuses light to give your room a soft glow
- Requires bulbs with medium (E26) base; T10 bulbs recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs
- Coordinates with other products in the Parallel collection



Available Colors/Finishes

Color tiles intended for reference only.

- | | | |
|---|-----|-----------------------|
|  | BNL | Brushed Nickel |
|  | CPL | Polished Chrome |
|  | BLL | Matte Black |
|  | 2GL | Brushed Moderne Brass |



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 06:15 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

UL 1598

CSA C22.2 No. 250.0

Technical Information

All product dimensions are nominal.

Number of Lights:	1
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	1
Hanging Type:	Non-hanging
Height:	10-5/8" (269 mm) - 10-5/8" (269 mm)

Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.

120 V, .05 A, 60 Hz

Warranty

See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-30-2026 06:15 - US-CA



Installation Notes

Install this product according to the installation instructions.

