



Parallel™ | K-35114-SC02

Two-light sconce

Features

- Etched opal glass gently diffuses light to give your room a soft glow
- Requires bulbs with medium (E26) base; T10 bulbs recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Includes installation hardware
- Fixture is dimmable when paired with dimmer switch and compatible bulbs
- Coordinates with other products in the Parallel collection



Available Colors/Finishes

Color tiles intended for reference only.

- | | | |
|---|-----|-----------------------|
|  | BNL | Brushed Nickel |
|  | CPL | Polished Chrome |
|  | BLL | Matte Black |
|  | 2GL | Brushed Moderne Brass |



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 06:15 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

UL 1598

CSA C22.2 No. 250.0

Technical Information

All product dimensions are nominal.

Number of Lights:	2
Lighting Type:	Socket-based
Socket Type:	E-26 Medium
Number of Shades:	2
Hanging Type:	Non-hanging
Height:	7-5/8" (193 mm) - 7-5/8" (193 mm)

Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Required Electrical Service

One circuit required.

120 V, 1 A, 60 Hz

Warranty


See website for detailed warranty information.

KOHLER® Indoor Lighting Fixtures Limited Warranty



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 06:15 - US-CA



Installation Notes

Install this product according to the installation instructions.

