

## Features

- Advanced spray engine provides three alternate experiences: wide coverage, intense drenching, and targeted spray
- Wide coverage spray produces an encompassing spray for everyday use
- Intense drenching spray delivers a forceful spray ideal for rinsing shampoo from hair
- Targeted spray is a focused stream for targeting sore muscles or use as a utility spray
- Thumb tab allows for a smooth transition between sprays
- Combination of balance, weight, grip, and angle makes this handshower comfortable and easy to use
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.5 gpm (9.5 lpm) handshower maximum flow rate at 80 psi (5.5 bar)
- 28" (711 mm) slidebar features adjustable mounting brackets for installation flexibility
- Box includes: Handshower, 28" (711 mm) slidebar with mounting brackets, 60" (1524 mm) metal hose
- Coordinates with other products in the Elate collection

## Material

- KOHLER finishes resist corrosion and tarnishing

## Included Components

K-33640-Y Three-function handshower, 2.5 gpm  
K-98341 27" slidebar



## Codes/Standards

ASME A112.18.1/CSA B125.1  
DOE - Energy Policy Act 1992


## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

| Color   | Code | Description                    |
|---|------|--------------------------------|
|  | CP   | Polished Chrome                |
|  | BN   | Vibrant® Brushed Nickel        |
|  | BL   | Matte Black                    |
|  | 2MB  | Vibrant® Brushed Moderne Brass |



## Technical Information

All product dimensions are nominal.

### Spout:

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

## Notes

For use with automatic compensating valves rated at 1.2 gal/min (4.5 l/min) or less.

Install this product according to the installation instructions.

**IMPORTANT:** K-35331 meets the Americans with Disability Act (ADA) and ICC A117.1 (specifically section 608.5) if installed properly and with part number K-26311.