



## Bellvu™ | K-35697-8L

56-5/8"-59-5/8" W x 75-3/4" H sliding shower door with 5/16"-thick Crystal Clear glass

### Features

- Dual sliding barn door style
- Innovative roller design with stainless steel bearings simplifies installation and provides out-of-plumb adjustability while glass is installed
- Controlled Close® innovative soft-close with double-dampening technology brings door to a secure close
- Frameless design emphasizes glass and creates a sleek, minimalist look
- 18" (457 mm) vertical handle accentuates the contemporary style
- Tempered glass ensures enhanced safety and durability
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- No wall jambs add to the minimalist look



### Available Colors/Finishes

*Color tiles intended for reference only.*

- SHP Bright Polished Silver
- BL Matte Black
- 2MB Vibrant Brushed Moderne Brass
- BNK Anodized Brushed Nickel



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.

9-12-2026 06:04 - US-CA

THE BOLD LOOK  
OF **KOHLER**

## Codes/Standards

ANSI Z97.1 (Tempered Glass)

CAN/CGSB-12.1

CPSC 16CFR 1201

---

## Technical Information

*All product dimensions are nominal.*

|                            |                   |
|----------------------------|-------------------|
| Base-To-Wall Radius –      | 1/2" (13 mm)      |
| Maximum:                   |                   |
| Shower Ledge Minimum Flat: | 2-1/2" (64 mm)    |
| Shower Wall Minimum Flat:  | 3-1/8" (79 mm)    |
| Weight:                    | 147 lbs (66.7 kg) |

---

## Material


- Frameless, heavy 5/16" (8 mm) thick Crystal Clear tempered glass
  - Anodized aluminum prevents rust and corrosion
- 

## Warranty

*See website for detailed warranty information.*

KOHLER® Bath and Shower Doors Ten-Year Limited  
Warranty





## Installation

- Fits opening widths 56-5/8" – 59-5/8" (1438 –1514 mm)
- 75-3/4" (1924 mm) high, with 69-1/2" (1765 mm) minimum head clearance
- 3" (76 mm) width adjustment
- 3/8" (10 mm) out-of-plumb adjustability on each side simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- For residential use only
- Not for use in hospitality
- Not for use with cast iron shower bases

## Installation Notes

*Install this product according to the installation instructions.*

The vertical opening should be a minimum of 78-3/4" (2000 mm) to allow for installation clearance.

