

KOHLER®

Portrait®

Two-piece elongated toilet, 1.6 gpf
K-3591-U

Features

- Two-piece design
- Elongated bowl offers added room and comfort
- 1.6 gpf (6.0 lpf)
- Left-hand Polished Chrome trip lever
- 2" (51 mm) fully glazed trapway
- Insuliner® tank liner minimizes condensation on the tank
- Combination consists of the K-4317 bowl and the K-4607 tank
- Coordinates with other products in the Portrait collection

Installation

- Standard 12" (305 mm) rough-in
- Three-bolt quick-connect installation
- Seat and supply line sold separately

Recommended Products/Accessories

- K-7637 Angle Supply with Stop (single)
- K-5588 Purefresh® Deodorizing elongated toilet seat
- K-4108 PureWash® E750 Elongated bidet toilet seat with remote control
- K-5420 Low-Profile Bolt Caps
- K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
IAPMO Certification

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

7-12-2024 23:29 - US

THE BOLD LOOK
OF **KOHLER®**



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Ingenium
Trap passageway:	2" (51 mm)
Water surface size:	10" x 9-3/4" (254 mm x 248 mm)
Rim to water surface:	5-3/4" (146 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.