

### Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Twin Touch™ flush offers a choice of 1.0 or 1.4 gallons per flush (gpf)
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Includes C3 toilet seat with bidet functionality
- Heated water sprays from two wands, adjustable for temperature, position, and spray motion
- Remote control with two programmable presets
- Automatic deodorization and nightlight
- Antimicrobial agent inhibits growth of odor-causing bacteria, mold, and mildew. This product does not protect users against bacteria, viruses, or other disease organisms. Always clean and wash this product thoroughly before and after each use
- For use only with the K-3607 and K-3825 toilets (comes included with those toilets)
- Antimicrobial agent inhibits growth of odor-causing bacteria, mold, and mildew. This product does not protect users against bacteria, viruses, or other disease organisms. Always clean and wash this product thoroughly before and after each use
- Dual-flush technology allows you to choose between a full or partial flush
- Power Lite® flushing technology uses an electric pump to deliver water from the tank through the bowl for extraordinarily powerful flushing
- Requires an electrical outlet near the toilet

### Recommended Products/Accessories

K-5588 Purefresh® Deodorizing elongated toilet seat  
K-4108 PureWash® E750 Elongated bidet toilet seat with remote control  
K-5420 Low-Profile Bolt Caps  
K-23726 Drain treatment



### Codes/Standards

ASME A112.19.2/CSA B45.1  
ASME A112.4.2/CSA B45.16  
UL Listed


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



# San Raphael®

One-piece elongated toilet, dual-flush  
**K-3607**



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor

Bowl shape: Elongated

Flush type: Power Lite

Trap passageway: 2-1/8" (54 mm)

Water surface size: 12" x 10" (305 mm x 254 mm)

Rim to water surface: 5-7/8" (149 mm)

Rough-in: 12" (305 mm)

Seat-mounting holes: 5-1/2" (140 mm)

Electrical component Pump: 120 V, 8.5 A, 60 Hz rating:

### Fixture Supply Requirements

Min static pressure: 15 psi (103.4 kPa)

### Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.