


KOHLER[®] Faucets

Fluence™

Three-way thermostatic bath & shower column with rainhead and three-function handshower, 9.5 lpm
K-36420T-9

Features

- Modern, simplistic exposed thermostatic valve serves as a hub for bath and shower controls
- Includes single-function rainhead, three-function handshower, 59" (1500 mm) hose, and shower column with integrated handshower holder
- Mechanically controlled thermostatic mixing valve maintains outlet temperature throughout shower experience
- Two Knob handles: One for temperature and volume control, the other for outlet selection
- 12" (305 mm) single-function round rainhead features full coverage with WaterMind™ technology, a drenching spray experience ideal for rinsing shampoo from hair
- Rainduet™ three-function handshower offers three spray experiences: full coverage with WaterMind™ technology, powerful massage, and gentle mist
- Full coverage with WaterMind™ technology delivers a consistent, drenching spray experience despite changes in water pressure
- Massage spray: Targeted, pulsing streams of water massage and ease muscles
- Gentle mist spray restores, with a thick cloud of silky, super-fine water droplets
- Three buttons located on the handshower face allow for easy transition between sprays
- Adjustable handshower holder locks in place at your preferred height
- Column height can be adjusted to suit users' preferences
- 2.5 gpm (9.5 lpm) maximum flow rate at 45 psi (3.1 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance



Codes/Standards

Plumbing Standards
QB/T 2806

See website for detailed warranty information.

Material


- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- With WaterMind™ technology, spray nozzles automatically adjust to changes in water pressure for a consistent shower under varying intensities

Installation

- Valve is fully serviceable from control panel
- Wall-mount
- G 1/2 (13 mm) inlet connection



Technical Information

All product dimensions are nominal.

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Shower Valve:

Flow Rate (Max) @ 45 psi 2.5 gal/min (9.5 l/min)

Manufacturer's minimum rated flow: 2.2 gal/min (8.3 l/min)

Pressure: 45 psi (3.1 bar)

Maximum (Static) Pressure: 125 psi (8.6 bar)

Minimum (Operating) Pressure: 15 psi (1 bar)

Notes

Install this product according to the installation instructions.

For use with showerheads or handsprays rated at 2.2 gal/min (8.3 l/min) or higher.