



8 Degree™ | K-3673

33" undermount single-bowl kitchen sink

Features

- 36" minimum base cabinet width
- Single bowl
- 9-3/4" depth provides generous workspace
- Offset drain increases workspace in the sink and storage space underneath
- Includes installation hardware, wineglass rack, and bottom sink rack



Codes/Standards

ASME A112.19.3/CSA B45.4

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Single Bowl
Basin Length:	31-1/2" (800 mm)
Basin Width:	16-1/2" (419 mm)
Basin Depth:	9-3/4" (248 mm)

Material

- Premium 16-gauge stainless steel
- Premium 16-gauge stainless steel

Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

K-8801 Sink drain and strainer with tailpiece


K-8799 Sink drain and strainer basket, less tailpiece

Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





Installation

- Undermount

Installation Notes

Install this product according to the installation instructions.

