



K-36750

32-1/2" undermount double-bowl kitchen sink

Features

- 36" (914 mm) minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Center drains
- Rounded 3/8" (10 mm) corners are easy to clean
- Matte finish offers rich, dimensional color
- Includes two bottom sink racks



Available Colors/Finishes

Color tiles intended for reference only.

- CM6 Matte White
- CM7 Matte Graphite
- CM2 Matte Brown
- CM1 Matte Black
- CM3 Matte Taupe
- CM4 Matte Grey



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
8-13-2026 20:00 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA B45.5/IAPMO Z124

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-7/8" (98 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Equal Bowls




Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
 - Solid color throughout the sink
 - Heat-resistant up to 750°F
 - Scratch-, stain-, chip-, and thermal-shock-resistant
-

Warranty

See website for detailed warranty information.





Installation

- Undermount
- Installation hardware and templates included

Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-13-2026 20:00 - US-CA