



K-36751

17-1/2" undermount bar sink

Features

- 21" (533 mm) minimum base cabinet width
- Single bowl
- 9" (229 mm) depth provides generous workspace
- Rear drain placement increases cabinet storage space underneath sink
- Rounded 3/8" (10 mm) corners are easy to clean
- Matte finish offers rich, dimensional color
- Includes sink rack



Available Colors/Finishes

Color tiles intended for reference only.

- CM6 Matte White
- CM7 Matte Graphite
- CM1 Matte Black
- CM3 Matte Taupe
- CM2 Matte Brown
- CM4 Matte Grey



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
8-13-2026 20:00 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

CSA B45.5/IAPMO Z124

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-7/8" (98 mm)
Minimum Base Cabinet Width:	21" (533 mm)
Basin Configuration:	Single Bowl
Basin Length:	15-1/4" (387 mm)
Basin Width:	16-9/16" (421 mm)
Basin Depth:	8" (203 mm)




Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

Warranty

See website for detailed warranty information.





Installation

- Undermount
- Installation hardware and templates included

Installation Notes

Install this product according to the installation instructions.



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

8-13-2026 20:00 - US-CA