

KOHLER®

San Raphael®
One-piece elongated toilet with skirted trapway, 1.28
gpf
K-3722

Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- 1.28 gpf (4.8 lpf)
- Skirted trapway simplifies cleaning
- Quiet-Close™ elongated lid and seat prevents slamming
- Quick-Release™ functionality allows seat to be removed easily from toilet for convenient cleaning
- Overhanging lid design creates a clean and sleek look
- Eligible for consumer rebates in some municipalities

Installation

- Standard 12" (305 mm) rough-in
- Supply line sold separately
- Requires mounting plate for heated seat installation (sold separately)

Recommended Products/Accessories

K-4108 PureWash® E750 Elongated bidet toilet seat with remote control
1023457 Wax Ring/Hardware Kit
1265114 Connector Hose
K-23726 Drain treatment
1362736 Mounting Plate Kit Exposed Wire



Codes/Standards

ASME A112.19.2/CSA B45.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

12-9-2024 23:27 - US/CA

THE BOLD LOOK
OF **KOHLER®**



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Siphon jet
Trap passageway:	2-1/16" (52 mm)
Water surface size:	11-1/2" x 7" (292 mm x 178 mm)
Rough-in:	12" (305 mm)
Template:	1231981-7, required, included

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.