

KOHLER® Faucets

Single-handle wall-mount kitchen sink faucet, cold-only

Cuff®
K-37314IN-4

Features

- Swing arm rotates 180° for full sink coverage
- For use with cold water line only
- 7.9 inch (201 mm) spout reach
- Single Lever handle provides on/off activation and volume control
- 6.4 gpm (24.2 lpm) maximum flow rate at 60 psi (4.1 bar)
- Aerated flow
- Includes valve

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Single-hole installation



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation instructions.