



Synthos™

45-3/4" undermount single-bowl kitchen sink

K-37907

Features

- 45-3/4" sink designed for a 48" minimum cabinet space
- Single bowl
- 11-1/16" (281 mm) bowl depth
- The three-tiered ledge design ensures optimal positioning of accessories, creating a seamless workflow
- Box includes: Sink, drain cover, and two dishwasher-safe sink racks
- The sink bowl features a generous slope, directing water and debris towards the drain for easy cleaning
- Offset drain increases workspace in the sink, includes drain cover that lifts for easy cleaning and a discreet barrier-free water flow
- SilentShield® sound-absorption technology offers quieter performance

Material

- Premium 16-gauge stainless steel

Installation

- Undermount

Included Components

- K-37924 Sink rack (Qty 2)
- K-37925 Drain cover




Codes/Standards

ASME A112.19.3/CSA B45.4

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl

Min. base cabinet width: 48" (1219 mm)

Bowl area (Basin #1):
 Length: 44" (1118 mm)
 Width: 15-9/16" (395 mm)
 Water depth: 12-7/8" (327 mm)

Drain hole: 3-3/4" (95 mm)

Template: Undermount, 1598274-7, required, not included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.

For proper fit of workstation accessories, the design requires a 1/2" (13mm) reveal on the front and back flanges, and the cutout template **MUST** be followed.