


Features

- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Compact elongated bowl offers added comfort while requiring less space
- Rim-to-floor height: 15-3/4" (400 mm)
- Dual-flush offers a choice of 0.8 or 1.28 gpf (3.0 or 4.5 lpf)
- Left-hand Polished Chrome trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Fully skirted trapway simplifies cleaning
- Class Five™ canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush

Installation


- Standard 12" (305 mm) rough-in
- Seat and supply line sold separately



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Flush type:	Class Five
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-5/16" (160 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation instructions.