

Features

- The Hint lighting collection complements both contemporary and traditional decor and creates a beautiful accent in any space
- Etched glass disks gently diffuse their light and give your room a soft glow
- Requires bulbs with medium (E26) base; type T or B bulbs recommended (sold separately)
- Suitable for damp locations, per UL 1598
- Coordinates with products in the Hint® collection
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Installation

- Wall-mount



Codes/Standards

UL 1598
CSA C22.2 No. 250.0



KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	BNL	Brushed Nickel
	CPL	Polished Chrome
	BLL	Matte Black
	2GL	Brushed Moderne Brass



Required Electrical Service

One circuit required.

120 V, 1 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material: Glass, Aluminum, Steel, Brass

Number of Lights: 2

Lighting Type: Socket-based

Socket Type: E-26 Medium

Number of Shades: 2

Shade Type: Etched Glass

Hanging Type: Non-hanging

Notes

Install this product according to the installation instructions.