

Features

- Frosted glass shades perfectly diffuse the light, reducing glare in the bathroom
- Coordinates with other products in the Bellera collection
- Suitable for damp locations, per UL 1598
- Requires bulbs with medium (E26) base; type A19 bulb recommended (sold separately)
- Fixture is dimmable when paired with dimmer switch and compatible bulbs

Material

- Premium metal and glass construction
- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes

Installation

- Wall-mount



Codes/Standards

UL 1598
CSA C22.2 No. 250.0


KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|-----------------|
|  | BNL | Brushed Nickel |
|  | CPL | Polished Chrome |



Technical Information

All product dimensions are nominal.

Material: Steel, Glass, Ceramic

Number of Shades: 3

Shade Type: Frosted Glass

Hanging Type: Non-hanging

Height: -

Notes

Install this product according to the installation guide.