



C1™ | K-38441-0FNC

Three-person Indoor Sauna

Features

- Scandinavian spruce interior and exterior walls exude a light, welcoming warmth
- 22-7/8" (580 mm) -deep solid obeche wood bench with matching backrest, headrest, and stool offers a relaxing repose for up to three users
- Digital control panel mounts externally to front of unit for easy access to control temperature, time, and backrest lighting, and allows versatility to install sauna into virtually any space
- Freestanding FERO 4.5 kW heater with obeche wood railing for a traditional sauna bathing experience
- 2700k warm white indirect lighting gently illuminates cabin
- 2-1/8" (54 mm) -thick mineral wool insulation between walls maximizes heat retention
- 5/16" (8 mm) tempered glass entry door aids in heat retention
- Back-to-back 10-5/8" (270 mm) beech wood handles remain cool to the touch
- Interior wall-mounted thermometer and beech wood 20-minute hourglass sand timer to monitor sauna session
- Includes complete sauna cabin with heater/stones, control panel, benches, backrest lighting, stool, thermometer, sandtimer, headrest, installation hardware
- Aerotherm ventilation system ensures adequate supply of oxygen and air exchange inside cabin
- Tongue-and-groove walls, floor, and roof connections for a seamless appearance and high-performance
- Dual thermostatic control provides a safe, consistent, and repeatable sauna experience
- Rubber door seal helps prevent warmed air from leaving cabin



Available Color

Color tile intended for reference only

 SPS Scandinavian Spruce

Technical Information

Minimum Floor Loading Requirements:	58.9 lbs/ft ² (287.5 kg/m ²)
Outlet specification:	NEMA 6-30P
Product weight:	760.725 lbs (345.06 kg)
Shipping weight:	1047.38 lbs (475.08 kg)

Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Heater:	4.5 kW
Required electrical service:	220 - 240 V, 30 A, 50/60 Hz
Electrical component rating:	240 V, 30 A, 50/60 Hz

Material

- Scandinavian spruce, obeche, and beech wood construction
- Tempered glass
- Durable matte aluminum door hinges

Codes & Standards


- UL 875
- CSA C22.2 No. 164

Recommended Products/Accessories

- K-35693 Three-person Indoor Sauna Floor Kit
- K-39194 Three-person Indoor Sauna Roof Kit
- 39814-A4 Recharge Essential Oil
- 39814-A1 Sleep Essential Oil
- 39814-A2 Breathe Essential Oil
- 39814-A6 Relax Essential Oil

Warranty

KOHLER® Sauna Limited Warranty



Installation

Freestanding or alcove

Installation Notes

Install this product according to the installation instructions.