KOHLER Faucets

Engage™

Single-handle bathroom sink faucet, 10 lpm

K-38462IN-4ND

Features

- Sleek and contemporary design
- Single Lever handle allows for both volume and temperature control
- 120 mm (4.75 inch) spout reach
- 97 mm (3.83 inch) spout height
- 10 lpm (2.64 gpm) maximum flow rate at 3.0 bar (43.51 psi)
- Aerated flow
- Coin aerator is easy to remove for maintenance
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Drain sold separately

Material

- Premium brass construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation
- G 1/2 connection



Codes/Standards

None Applicable

KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold

KOHLER. Faucets

Engage™

Single-handle bathroom sink faucet, 10 lpm

K-38462IN-4ND



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation instructions.