



Reach™
Hidden cord one-piece elongated toilet with skirted
trapway, 4.2 lpf
K-3856T-MHC

Features


- Part of the Reach™ collection
- One-piece toilets integrate the tank and bowl into a seamless, easy-to-clean design
- Elongated bowl offers added room and comfort
- 1.1 gpf (4.2 lpf)
- Rim-to-floor height: 15-1/2" (394 mm)
- Left-hand Polished Chrome trip lever
- 1-15/16" (49 mm) fully glazed trapway
- Skirted trapway simplifies cleaning
- Hidden cord design conceals bidet seat cords (bidet seat sold separately)

Material

- Vitreous china

Installation


- Standard 12" (305 mm) rough-in
- Floor-mount
- Seat and supply line sold separately



Codes/Standards

Plumbing Standards
GB 25502
GB/T 6952

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Class Five
Trap passageway:	1-15/16" (49 mm)
Rim to water surface:	6-1/2" (165 mm)

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.