

Features

- Contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- 7.19 inch (183 mm) nondiverter bath spout with G 1/2 (13 mm) connection
- 10.0 lpm (2.64 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- For single-hole installation
- Wall-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	RGD	Vibrant Rose Gold
	BRD	Vibrant Brushed Rose Gold



Technical Information

All product dimensions are nominal.

Spout:

Spout reach: 7-3/16" (183 mm)

Notes

Install this product according to the installation instructions.