



Staccato™ | K-3891

31-3/4" undermount double-bowl kitchen sink

Features

- 36" minimum base cabinet width
- Large/medium bowls
- 8" (203 mm) depth



Sustainability



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-29-2026 19:01 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ASME A112.19.3/CSA B45.4

Technical Information

All product dimensions are nominal.

Drain Hole Diameter:	3-5/8" (92 mm)
Minimum Base Cabinet Width:	36" (914 mm)
Basin Configuration:	Large Bowl on Left

Material

- Premium 18-gauge stainless steel

Recommended Products/Accessories


- K-23726 Drain treatment
- K-23729 Stainless steel cleaner
- K-5103 Stainless steel large sink rack, 16-5/8" x 15-7/8"
- K-5111 Stainless steel small sink rack, 9-5/8" x 15-7/8"
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket, less tailpiece

Warranty

See website for detailed warranty information.

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





Installation

- Undermount

Installation Notes

Install this product according to the installation instructions.

Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.

