

Features

- Sleek, minimalist design
- Single handle provides on/off activation, volume, and temperature control
- Red/blue indexing on handle
- Includes faceplate with Lever handle and diverter sleeve
- Coordinates with other products in the Hone® collection to complete your bathroom

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Trim only; requires Aqua Turbo™ 235 valve to complete installation (sold separately)



Codes/Standards

None Applicable



KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Shower Valve:

Flow Rate (Max) @ 45 psi	8 gal/min (30.3 l/min)
Manufacturer's minimum rated flow:	7.92 gal/min (30 l/min)
Pressure:	45 psi (3.1 bar)
Maximum (Static) Pressure:	125 psi (8.6 bar)
Minimum (Operating) Pressure:	20 psi (1.4 bar)

Notes

Install this product according to the installation guide.

For use with showerheads or handsprays rated at 7.92 gal/min (30 l/min) or higher.