



# Staccato™ | K-3899

31-3/4" undermount double-bowl kitchen sink

## Features

- Fits minimum 36" (914 mm) apron sink base cabinet
- Double-equal bowls
- 8" (203 mm) depth
- Includes installation hardware



## Codes/Standards

ASME A112.19.3/CSA B45.4

## Technical Information

*All product dimensions are nominal.*

|                             |                    |
|-----------------------------|--------------------|
| Drain Hole Diameter:        | 3-5/8" (92 mm)     |
| Minimum Base Cabinet Width: | 36" (914 mm)       |
| Basin Configuration:        | Equal Bowls        |
| Basin Length:               | 13-15/16" (354 mm) |
| Basin Width:                | 17-1/16" (433 mm)  |
| Basin Depth:                | 8" (203 mm)        |

## Material

- Premium 18-gauge stainless steel

## Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

K-5117 Stainless steel large sink rack, 13-1/4" x 15-7/8", for right-hand bowl

K-5119 Stainless steel large sink rack, 13" x 15-3/4", for left-hand bowl

K-8801 Sink drain and strainer with tailpiece


K-8799 Sink drain and strainer basket, less tailpiece

## Warranty

*See website for detailed warranty information.*

KOHLER® Stainless Steel Sinks Lifetime Limited Warranty





## Installation

- Undermount

## Installation Notes

*Install this product according to the installation instructions.*

