



# Numi®

One-piece elongated smart toilet, dual-flush  
**K-3900**

## Features

- Compact, streamlined one-piece toilet
- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Hands-free opening and closing of seat
- Dual-flush offers a choice of 0.6 or 1.28 gpf (2.2 or 4.8 lpf)
- 2-7/8" (73 mm) trapway
- Advanced bidet functionality with integrated dryer
- Remote control
- Wall-mount docking station
- Supply line included
- Power cord
- Auxiliary music cord
- External FM antenna
- Dual-flush technology allows you to choose between a full or partial flush

## Installation

- Standard 12" (305 mm) rough-in
- Requires a supply stop with 1/2" OD compression male outlet thread

## Recommended Replacements

- This product is replaced by K-3901-NSR One-piece elongated smart toilet, dual-flush.

## Recommended Products/Accessories

K-23726 Drain treatment



## Codes/Standards

ASME A112.19.2/CSA B45.1

ASME A112.4.2/CSA B45.16

ASME A112.19.14

UL 1951

CSA C22.2 No. 14

CSA C22.2 No. 68

UL Listed

## KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty

See website for detailed warranty information.

**DISCONTINUED** This product has been discontinued.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

2-14-2025 16:50 - US

THE BOLD LOOK  
OF **KOHLER®**



**Numi®**  
One-piece elongated smart toilet, dual-flush  
**K-3900**



**DISCONTINUED**

This product has  
been discontinued.

### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Power
Trap passageway:	2-7/8" (73 mm)
Water surface size:	10" x 8-1/4" (254 mm x 210 mm)
Rim to water surface:	5-1/2" (140 mm)
Rough-in:	12" (305 mm)

### Fixture Supply Requirements

Min static pressure: 30 psi (206.8 kPa)

### Notes

Install this product according to the installation instructions.

Installation of a water hammer arrestor is recommended.

Install the docking station power cord and water hammer arrestor before installing the finished wall.

The supplied water inlet hose requires a supply stop with a 1/2" OD compression male outlet thread.

This model is fastened to the floor by mounting blocks. If local codes require the toilet be bolted to the flange, order flange installation kit 1171368 for required hardware and instructions.

Can be installed with water supply and electrical supply attached to the back wall or through the floor. See roughing-in illustration for details.

Adjust the through-the-floor installation as required to meet all local codes.

**DISCONTINUED**

This product has  
been discontinued.