



Numi® | K-3901-NSR

One-piece elongated smart toilet, dual-flush

Features

- Compact, streamlined one-piece smart toilet with integrated personal cleansing
- Elongated bowl offers added room and comfort
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Motion-activated, hands-free opening/closing of seat and cover
- Dual-flush offers a choice of 0.6 or 1.28 gpf (2.2 or 4.8 lpf)
- Advanced bidet functionality with self-cleaning wand, precision air dryer, and deodorizing filter all in one
- Heated seat and foot warmer
- Ambient lighting with eight colors and three programming options
- Touch-screen remote control with magnetic wall-mount docking/charging station
- Energy Save feature monitors usage and adjusts heated seat settings to save energy
- Emergency flush supports up to 100 flushes during power outage
- 2-7/8" (73 mm) trapway
- Dual-flush technology allows you to choose between a full or partial flush
- Advanced bidet functionality with self-cleaning wand, precision air dryer, and deodorizing filter all in one
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet (10 meters) away



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 19:17 - US-CA

THE BOLD LOOK
OF **KOHLER**®

Codes/Standards

Accessibility standards may require controls to be located on the open side of the toilet.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.



ASME A112.4.2/CSA B45.16

ASME A112.19.2/CSA B45.1

ASME A112.19.14

DOE - Energy Policy Act 1992

EPA WaterSense®

California Energy Commission (CEC)

UL 1951

CSA C22.2 No. 14

CSA C22.2 No. 68

cUL Listed

UL Listed

Technical Information

Rough-in:	Standard 12" (305mm)
Flush Type:	Power
Flush Rate:	0.6 or 1.28 gpf (2.2 or 4.8 lpf)
Bowl Shape:	Elongated
Waste Outlet:	Floor
Trapway Size:	2-7/8" (73 mm)
Trapway Type:	Skirted
Water Surface Size:	10" x 8-1/4" (254 mm x 210 mm)
Rim to Water Surface:	5-1/2" (140 mm)

Recommended Products/Accessories

1171368 FLANGE INSTALLATION KIT

K-23726 Drain treatment

Connectivity



The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license.

Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

Electrical Component Ratings

Power Cord Length: 56" (1422 mm)

Warranty

See website for detailed warranty information.

KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty




1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.

7-29-2026 19:17 - US-CA



Installation

- Standard 12" (305 mm) rough-in
- Requires a supply stop with 1/2" OD compression male outlet thread
- A drain line grade of 1/4" per foot minimum is required

Installation Notes

Install this product according to the installation instructions.

IMPORTANT! Use the supply hoses provided with the fixture. Do not reuse the previously installed hoses. Installation of a water hammer arrestor is recommended. Install the docking station cord, when premium remote control is included, before installing the finished wall. The supplied water inlet hose requires a supply stop with a 1/2" OD compression male outlet thread. If local codes require the toilet be bolted to the flange, order flange installation kit for required hardware and instructions. Can be installed with water and electrical supplies attached to the back wall or through the floor. See roughing-in illustration for details. Adjust the through-the-floor installation as required to meet all local codes.

