

## Claude™ by Studio McGee | K-39310

72" bathroom vanity cabinet with sinks and quartz top

### Features

- Designed in collaboration with Studio McGee
- Set includes cabinet, precut quartz vanity top, backsplash, sinks, cabinet hardware
- Two convenient tip-out drawers for storing smaller, frequently used items
- Full-extension 17" (432 mm) drawer with soft-close undermount slides
- Removable dividers in top drawers to personalize drawer organization
- Three-way adjustable soft-close door hinges for easy cabinet access
- 20-7/16" (519 mm) cabinet interior provides ample storage space
- Finish-matched cabinet interior offers generous clearance for plumbing
- Two internal electrical outlets and two USB ports for powering small devices
- Two stainless steel appliance holders for hairdryers, curling irons, or accessories
- Bianco Bella (GBB) quartz vanity top adds beauty and long-lasting durability
- Coordinates with Bianco Bella (GBB) quartz side splash (sold separately)
- Vanity top has single faucet hole at each sink location; requires deck-mount faucets (sold separately)
- Vibrant® Polished Nickel hardware included on White and Draper Oak vanities; Vibrant Brushed Moderne Brass hardware on White Oak vanities. Additional hardware finishes are available (sold separately)
- Includes optional finish-matched filler strip to close gap between vanity and wall if installed adjacent to wall



### Available Colors/Finishes

*Color tiles intended for reference only.*

- 0 White
- SWK White Oak
- DAK Draper Oak



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.  
For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
5-13-2026 12:0 - US-CA

---

## Codes/Standards

ASME A112.19.2/CSA B45.1  
EPA TSCA Title VI/CARB P2

---

## Technical Information

*All product dimensions are nominal.*

|                       |             |
|-----------------------|-------------|
| Lighting Included:    | No          |
| Number of Deck Holes: | 3           |
| Center(s):            | 8" (203 mm) |

---

## Material

- Vitreous china sinks
  - Solid and composite wood
  - Wood is a living material, and its beauty is enhanced by natural variations in grain, color, and pattern. No two pieces of wood are exactly the same, and the color will change with age, temperature, and exposure to light
- 

## Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Outlet: 120 V, 12 A, 60 Hz

## Electrical Component Ratings

Outlet: 120 V, 12 A, 60 Hz, 1440 W

Power Cord Length: 98.4" (2499 mm)

---


## Warranty

*See website for detailed warranty information.*

KOHLER® One-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)  
Kohler Co. reserves the right to make revisions without notice to product specifications.  
For the most current specification sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada.  
5-13-2026 12:0 - US-CA



## Installation

- Easy installation – no special tools required
- Sinks preinstalled on vanity top to simplify installation

## Installation Notes

*Install this product according to the installation instructions.*

Install this product in accordance with the installation instructions. Select the type of fastener based upon the wall material. Two 250 lb (113.4 kg) minimum load bearing fasteners are recommended with a lag bolt of length to clear obstacles in the wall and 5/16" washers. Calculate the proper lag bolt length by adding the 1-1/2" (38 mm) backing material, plus the wallboard thickness, plus the back rail thickness.

