


Features

- Round-front bowl
- Rim-to-floor height: 15-3/8" (390 mm)
- Dual-flush offers a choice of 1.1 or 1.8 gpf (4.0 or 7.0 lpf)
- Fully skirted trapway simplifies cleaning
- Stainless steel wand offers adjustable spray shape, position, water pressure, temperature, pulsate, and oscillate functions
- Front and rear wash modes provide warm water for cleansing
- Self-cleaning function uses UV light to automatically clean the wand surfaces
- Warm-air drying system with adjustable temperature settings
- Automatic deodorization system
- LED nightlight provides improved visibility in low-light conditions
- Heated seat with adjustable temperature settings
- Foot sensor allows for hands-free seat opening/closing and flush
- Soft-close lid and seat
- Emergency flush supports up to 100 flushes during power outage with simple touch-button activation
- Energy Save feature monitors usage and adjusts heated seat settings to save energy
- Automatic flushing after every use; flush can also be controlled by the remote control
- Includes complete toilet and seat, supply stop valve, braided inlet supply hose, power cord, and remote control

Installation


- 7-1/10" (180 mm) P-trap rough-in
- Requires dedicated electrical GFCI circuit (220 V, 10 A, 50 Hz)



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Wall
Flush type:	Power
Trap passageway:	1-11/16" (43 mm)
Rim to water surface:	5-1/4" (133 mm)

Notes

Install this product according to the installation instructions.