

Wellworth®

Two-piece elongated toilet, 1.28 gpf K-3998-UR

Features

- Two-piece design
- Elongated bowl offers added room and comfort
- Right-hand Polished Chrome trip lever
- Insuliner® tank liner minimizes condensation on the tank
- Coordinates with other products in the Wellworth collection
- KOHLERs canister flush valve harnesses the natural force of gravity and optimizes flushing performance
- 1.28 gpf (4.8 lpf)
- 2-1/8" (54 mm) fully glazed trapway
- Class Five® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush
- Includes tank, tank accessory pack, tank cover, trip lever, and bolt caps



- Standard 12" (305 mm) rough-in
- Three-bolt quick-connect installation
- Seat and supply line sold separately

Recommended Products/Accessories

K-5588 Purefresh® Deodorizing elongated toilet seat K-4108 PureWash® E750 Elongated bidet toilet seat with remote control K-5420 Low-Profile Bolt Caps K-9379 Trip Lever

1023457 Wax Ring/Hardware Kit 1265114 Connector Hose

K-23726 Drain treatment

Included Components

K-4198 Elongated toilet bowl K-4467-UR Toilet tank, 1.28 gpf





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty


See website for detailed warranty information.





KOHLER®

Two-piece elongated toilet, 1.28 gpf K-3998-UR



Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor
Bowl shape: Elongated
Flush type: Class Five
Trap passageway: 2-1/8" (54 mm)

Water surface size: 11-1/4" x 8-1/4" (286 mm x 210 mm)

Rim to water 5-1/4" (133 mm)

surface:

Rough-in: 12" (305 mm) Seat-mounting 5-1/2" (140 mm)

holes:

Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.

