

#### Features

- Scandinavian spruce interior exudes a light, welcoming warmth
- 22-7/8" (580 mm) -deep solid obeche wood bench with matching backrest, headrest, and stool offers a relaxing repose for up to three users
- Freestanding FERO 9.0 kW heater with obeche wood railing for a traditional sauna bathing experience
- 2700k warm white indirect lighting gently illuminates cabin
- Interior wall-mounted thermometer and beech wood 20-minute hourglass sand timer to monitor sauna session
- Dual thermostatic control provides a safe, consistent, and repeatable sauna experience
- Aerotherm ventilation system ensures adequate supply of oxygen and air exchange inside cabin
- Exterior clad in weathered grey spruce offers an organic, timeless elegance
- Digital control panel mounts externally to front of unit for easy access to control temperature, time, and backrest lighting, and allows versatility to install sauna into virtually any space. Cover securely locks to protect unit from the elements or unauthorized use
- Front door securely locks when not in use
- 2-1/8" (54 mm) -thick mineral wool insulation between walls maximizes heat retention
- Triple-insulated roof with two layers of mineral wool and air gap to prevent heat loss, followed by waterproof EPDM membrane
- 5/16" (8 mm) tempered glass entry door aids in heat retention
- Rubber door seal helps prevent warmed air from leaving cabin
- 10-5/8" (270 mm) beech wood handle remains cool to the touch
- Stainless steel exterior door handle
- Double pane insulated windows retain and evenly distribute heat throughout cabin
- Roof eaves extend to protect exterior from inclement weather, provide shade, and increase energy efficiency
- Exterior lighting surrounds sauna creating a warm atmosphere
- Tongue-and-groove walls, floor, and roof connections for a seamless appearance and high-performance
- Includes complete sauna cabin with heater/stones, control panel, benches, backrest lighting, stool, thermometer, sandtimer, headrest, installation hardware



#### Codes/Standards

UL 875  
CSA C22.2 No. 164

#### KOHLER® Sauna Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	WGS	



#### Material

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

2-13-2026 08:15 - US



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Heater: 220-240 V, 50 A, 50/60 Hz

### Technical Information

All product dimensions are nominal.

Weight: 2469.6 lbs (1120.2 kg)

Electrical component Heater: 240 V, 50 A, 50/60 Hz rating:

### Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.