



Karing®

One-piece elongated smart toilet, 1.28 gpf
K-4026

Features

- Compact, streamlined one-piece smart toilet with integrated personal cleansing
- Elongated bowl offers added room and comfort
- 1.28 gpf (4.8 lpf)
- Advanced bidet functionality with self-cleaning wand, precision air dryer, and deodorizing filter all in one
- Personalized settings for two users for heated seat, dryer, and water temperature
- Intuitive touch-screen remote is hand-held or wall-mounted
- Motion-activated, hands-free opening/closing of cover
- LED lighting illuminates the bowl to serve as a nightlight
- Self-cleaning wand automatically performs rinse cycle after each use
- Carbon filter neutralizes odors for up to a year
- Power Lite® flushing technology offers a powerful 1.28-gallon flush that is controlled from either the touch screen or integrated remote
- Minimum static pressure of 20 psi required
- Eligible for consumer rebates in some municipalities

Installation

- Standard 12" (305 mm) rough-in
- Requires dedicated electrical GFCI circuit (120 V, 15 A, 60 Hz)

Recommended Products/Accessories

K-23726 Drain treatment




Codes/Standards

ASME A112.19.2/CSA B45.1
ASME A112.4.2/CSA B45.16
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
UL 1951
CSA C22.2 No. 14
CSA C22.2 No. 68
cUL Listed
UL Listed

KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Toilet type:	Floor-mount
Waste Outlet:	Floor
Bowl shape:	Elongated
Flush type:	Power Lite
Trap passageway:	2-7/8" (73 mm)
Water surface size:	12" x 9-1/2" (305 mm x 241 mm)
Rim to water surface:	4-7/8" (124 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Fixture Supply Requirements

Min static pressure: 20 psi (137.9 kPa)

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

2-14-2025 23:00 - US/CA

Notes

Install this product according to the installation instructions.

This product is designed for installation with the electrical and water supplies located through either the wall or the floor.

If the rough-in distance is less than 12" (305 mm) the seat may strike the wall when it is opened. Confirm the rough-in is 12" (305 mm) before installing the toilet.