



Highline® | K-4304-SSL

Elongated toilet bowl with bedpan lugs

Features

- Combine with K-4645 Highline toilet tank to create K-3493 Highline Pressure Lite toilet 1.6 gpf
- Constructed of vitreous china.
- Combine with K-4484 Highline toilet tank to create K-3519 Highline Pressure Toilet 1.0 gpf
- 1.0 gpf (3.8 lpf) when combined with a K-4484 tank
- The ultra-low water consumption is ideal for water conservation and can help earn Water Efficiency points in the LEED® Green Building Rating System
- Bedpan lugs included
- Antimicrobial finish inhibits the growth of mold-, mildew-, stain-, and odor-causing bacteria on the fixture surface. This product does not protect users against bacteria, viruses, or other disease organisms. Always clean and wash this product thoroughly before and after each use
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults



Codes/Standards

Accessibility standards may require controls to be located on the open side of the toilet.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

ASME A112.19.2/CSA B45.1

Technical Information

Rough-in:	Standard 12" (305mm)
Flush Type:	Pressure Lite
Bowl Shape:	Elongated
Waste Outlet:	Floor
Trapway Size:	2-1/4" (57 mm)
Trapway Type:	Exposed

Recommended Products/Accessories

K-4484 Toilet tank, 1.0 gpf

K-4645 Toilet tank, 1.6 gpf

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty



No image available.
This product is a component and not intended to be a standalone installation.

Installation

- Standard 12" (305 mm) rough-in

Installation Notes

Install this product according to the installation instructions.

