

Stratton[™] Water-Guard®

Flushometer valve elongated blow-out toilet bowl K-4450-C

Features

- Elongated bowl offers added room and comfort
- Blow-out
- 1-1/2" (38 mm) top spud
- 3.5 gpf (13.2 lpf)
- 14-1/2" (368 mm) x 11-3/8" (289 mm) water area

Material

Vitreous china

Installation

- Wall-mount
- This product is not designed or intended for bariatric use

Recommended Products/Accessories

K-4670-C Lustra[™] Elongated toilet seat with check hinge K-4670-CA Lustra[™] Commercial elongated toilet seat with antimicrobial agent and check hinge





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 ADA ICC/ANSI A117.1 CSA B651 OBC IAPMO Certification

KOHLER[®] One-Year Limited Warranty


See website for detailed warranty information.





Stratton[™] Water-Guard®

Flushometer valve elongated blow-out toilet bowl K-4450-C



Technical Information

All product dimensions are nominal.	
Toilet type:	Wall-mount
Waste Outlet:	Wall
Bowl shape:	Elongated
Spud size:	1-1/2", Inlet, Top
Trap passageway:	2-3/4" (70 mm)
Water surface size:	14-1/2" x 11-3/8" (368 mm x 289 mm)
Rim to water surface:	5-3/8" (137 mm)
Seat-mounting holes:	5-1/2" (140 mm)

Fixture Supply Requirements

Min static pressure:	45 psi (310.3 kPa)
Max static pressure:	80 psi (551.6 kPa)
Min flowing	35 psi (241.3 kPa)
pressure:	
Min flow rate:	35 gpm (132.5 lpm)

Notes

Install this product according to the installation instructions.

Refer to manufacturer and local codes for flush valve requirements.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.

