



# Suffield™ Water-Guard®

Flushometer valve elongated blow-out toilet bowl  
**K-4475-C**

## Features

- 1-1/2" (38 mm) rear spud
- Elongated bowl offers added room and comfort
- Includes integral seat

## Recommended Products/Accessories

K-23726 Drain treatment



ADA

CSA B651

OBC

## Codes/Standards

ASME A112.19.2/CSA B45.1

DOE - Energy Policy Act 1992

ADA

ICC/ANSI A117.1

CSA B651

OBC

## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada


2-14-2025 23:14 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



# Suffield™ Water-Guard®

Flushometer valve elongated blow-out toilet bowl  
K-4475-C



## Technical Information

All product dimensions are nominal.

Toilet type:	Wall-mount
Waste Outlet:	Wall
Bowl shape:	Elongated
Spud size:	1-1/2", Inlet, Rear
Trap passageway:	2-5/8" (67 mm)
Water surface size:	14-3/8" x 11-1/4" (365 mm x 286 mm)
Rim to water surface:	5-3/8" (137 mm)
Seat-mounting holes:	5-1/2" (140 mm)

## Fixture Supply Requirements

Min static pressure:	45 psi (310.3 kPa)
Max static pressure:	80 psi (551.6 kPa)
Min flowing pressure:	35 psi (241.3 kPa)
Min flow rate:	35 gpm (132.5 lpm)

## Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

Plumbing codes may require elongated toilets and elongated, open-front seats in public bathrooms.

Accessibility standards may require controls to be located on the open side of the toilet.